

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781271

Luminaire Tested: LER4D40BD010-EC4DR3540509040-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781271
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D40BD010-EC4DR3540509040-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3803.3 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781271

CATALOG NUMBER: LER4D40BD010-EC4DR3540509040-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P781271

CATALOG NUMBER: LER4D40BD010-EC4DR3540509040-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96		
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88		
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84		
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81		
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78		
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75		
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72		
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70		
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1143370
5°	1116512
10°	1006272
15°	781026
20°	442988
25°	172347
30°	64293
35°	35240
40°	23035
45°	14015
50°	8924
55°	6305
60°	4611
65°	2508
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14015 cd/sqm



TEST NUMBER: P781271

CATALOG NUMBER: LER4D40BD010-EC4DR3540509040-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	936.2	24.6
10°-20°	1828.0	48.1
20°-30°	745.5	19.6
30°-40°	178.4	4.7
40°-50°	74.3	2.0
50°-60°	30.8	0.8
60°-70°	9.6	0.3
70°-80°	0.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3509.7	92.3
0°-40°	3688.1	97.0
0°-60°	3793.2	99.7
0°-90°	3803.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3803.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10465	
5°	10180	936
15°	6905	1828
25°	1430	746
35°	264	178
45°	91	74
55°	33	31
65°	10	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781271

CATALOG NUMBER: LER4D40BD010-EC4DR3540509040-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	10464.6
2.5°	10401.9
5°	10179.9
7.5°	9737.0
10°	9069.9
12.5°	8130.5
15°	6904.7
17.5°	5405.5
20°	3809.9
22.5°	2429.4
25°	1429.6
27.5°	808.1
30°	509.6
32.5°	357.8
35°	264.2
37.5°	204.3
40°	161.5
42.5°	124.4
45°	90.7
47.5°	67.9
50°	52.5
52.5°	41.7
55°	33.1
57.5°	26.8
60°	21.1
62.5°	15.4
65°	9.7
67.5°	3.4
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)