

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781293

Luminaire Tested: LER4D40BD010-EC4DR4040509040-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781293
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D40BD010-EC4DR4040509040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4372.8 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781293

CATALOG NUMBER: LER4D40BD010-EC4DR4040509040-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781293

CATALOG NUMBER: LER4D40BD010-EC4DR4040509040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1112373
5°	1106970
10°	1046334
15°	889514
20°	606270
25°	252962
30°	79533
35°	36974
40°	20439
45°	9379
50°	4555
55°	2495
60°	1289
65°	465
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9379 cd/sqm



TEST NUMBER: P781293

CATALOG NUMBER: LER4D40BD010-EC4DR4040509040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	942.4	21.6
10°-20°	2111.3	48.3
20°-30°	1056.8	24.2
30°-40°	193.7	4.4
40°-50°	53.5	1.2
50°-60°	12.5	0.3
60°-70°	2.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4110.5	94.0
0°-40°	4304.3	98.4
0°-60°	4370.3	99.9
0°-90°	4372.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4372.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10181	
5°	10093	942
15°	7864	2111
25°	2098	1057
35°	277	194
45°	61	53
55°	13	13
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781293

CATALOG NUMBER: LER4D40BD010-EC4DR4040509040-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	10180.9
2.5°	10166.1
5°	10092.9
7.5°	9859.8
10°	9431.0
12.5°	8762.5
15°	7863.8
17.5°	6695.1
20°	5214.2
22.5°	3554.8
25°	2098.3
27.5°	1109.2
30°	630.4
32.5°	407.4
35°	277.2
37.5°	198.1
40°	143.3
42.5°	98.1
45°	60.7
47.5°	38.7
50°	26.8
52.5°	19.0
55°	13.1
57.5°	8.3
60°	5.9
62.5°	3.6
65°	1.8
67.5°	1.2
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)