

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781173

Luminaire Tested: LER4D35BD010-EC4DR6520359040-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P781173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR6520359040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3117.8 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781173

CATALOG NUMBER: LER4D35BD010-EC4DR6520359040-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781173

CATALOG NUMBER: LER4D35BD010-EC4DR6520359040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	165336
5°	164918
10°	164779
15°	159698
20°	145386
25°	126692
30°	105373
35°	83497
40°	60261
45°	38068
50°	19844
55°	10549
60°	5537
65°	3040
70°	1281
75°	1399
80°	975
85°	804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38068 cd/sqm



TEST NUMBER: P781173

CATALOG NUMBER: LER4D35BD010-EC4DR6520359040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.7	8.6
10°-20°	733.1	23.5
20°-30°	896.1	28.7
30°-40°	727.1	23.3
40°-50°	362.3	11.6
50°-60°	101.1	3.2
60°-70°	23.0	0.7
70°-80°	6.0	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1896.9	60.8
0°-40°	2624.0	84.2
0°-60°	3087.4	99.0
0°-90°	3117.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3117.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2831	
5°	2813	268
15°	2641	733
25°	1966	896
35°	1171	727
45°	461	362
55°	104	101
65°	22	23
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P781173

CATALOG NUMBER: LER4D35BD010-EC4DR6520359040-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2830.9
2.5°	2828.8
5°	2813.0
7.5°	2803.9
10°	2778.5
12.5°	2726.9
15°	2641.2
17.5°	2507.3
20°	2339.2
22.5°	2157.8
25°	1966.0
27.5°	1761.0
30°	1562.5
32.5°	1366.6
35°	1171.1
37.5°	976.0
40°	790.4
42.5°	616.5
45°	460.9
47.5°	321.2
50°	218.4
52.5°	150.6
55°	103.6
57.5°	69.9
60°	47.4
62.5°	32.9
65°	22.0
67.5°	11.2
70°	7.5
72.5°	7.1
75°	6.2
77.5°	4.2
80°	2.9
82.5°	2.1
85°	1.2
87.5°	0.8
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)