

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781180

Luminaire Tested: LER4D35BD010-EC4DR7020359024-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781180
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR7020359024-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2708.3 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781180

CATALOG NUMBER: LER4D35BD010-EC4DR7020359024-4LBS1B

Luminous Intensity Polar Plot



CATALOG NUMBER: LER4D35BD010-EC4DR7020359024-4LBS1B

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93	93	93	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78	78	78	78			
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71	71	71	71			
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65	65	65			
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60	60	60	60			
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56	56	56	56			
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	51	51			
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48	48	48	48			
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44	44	44	44			

	0°
0°	233556
5°	232967
10°	232466
15°	232406
20°	230127
25°	216181
30°	192727
35°	153657
40°	102037
45°	61004
50°	31616
55°	16630
60°	5878
65°	103
70°	0
75°	0
80°	0
85°	0

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 61004 cd/sqm



TEST NUMBER: P781180

CATALOG NUMBER: LER4D35BD010-EC4DR7020359024-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.0	7.5
10°-20°	579.4	21.4
20°-30°	817.3	30.2
30°-40°	705.6	26.1
40°-50°	315.9	11.7
50°-60°	82.7	3.1
60°-70°	5.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1598.7	59.0
0°-40°	2304.2	85.1
0°-60°	2702.9	99.8
0°-90°	2708.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2708.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2138	
5°	2124	202
15°	2055	579
25°	1793	817
35°	1152	706
45°	395	316
55°	87	83
65°	0	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781180

CATALOG NUMBER: LER4D35BD010-EC4DR7020359024-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2137.6
2.5°	2135.3
5°	2124.1
7.5°	2114.9
10°	2095.3
12.5°	2077.6
15°	2054.6
17.5°	2028.1
20°	1979.2
22.5°	1898.9
25°	1793.2
27.5°	1670.6
30°	1527.6
32.5°	1352.7
35°	1152.0
37.5°	930.6
40°	715.4
42.5°	543.5
45°	394.8
47.5°	272.1
50°	186.0
52.5°	128.4
55°	87.3
57.5°	52.7
60°	26.9
62.5°	8.5
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report







(END OF REPORT)