

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781199

Luminaire Tested: LER4D35BD010-EC4DR7020359040-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D35BD010-EC4DR7020359040-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3410.6 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781199

CATALOG NUMBER: LER4D35BD010-EC4DR7020359040-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P781199

CATALOG NUMBER: LER4D35BD010-EC4DR7020359040-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56		
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	294119
5°	293389
10°	292754
15°	292674
20°	289810
25°	272239
30°	242701
35°	193512
40°	128495
45°	76811
50°	39826
55°	20935
60°	7408
65°	129
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 76811 cd/sqm



TEST NUMBER: P781199

CATALOG NUMBER: LER4D35BD010-EC4DR7020359040-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	254.4	7.5
10°-20°	729.6	21.4
20°-30°	1029.2	30.2
30°-40°	888.5	26.1
40°-50°	397.9	11.7
50°-60°	104.2	3.1
60°-70°	6.8	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2013.2	59.0
0°-40°	2901.7	85.1
0°-60°	3403.8	99.8
0°-90°	3410.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3410.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2692	
5°	2675	254
15°	2587	730
25°	2258	1029
35°	1451	889
45°	497	398
55°	110	104
65°	0	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781199

CATALOG NUMBER: LER4D35BD010-EC4DR7020359040-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2691.9
2.5°	2689.0
5°	2675.0
7.5°	2663.4
10°	2638.7
12.5°	2616.4
15°	2587.4
17.5°	2554.0
20°	2492.5
22.5°	2391.3
25°	2258.2
27.5°	2103.8
30°	1923.7
32.5°	1703.4
35°	1450.8
37.5°	1171.9
40°	900.9
42.5°	684.5
45°	497.1
47.5°	342.7
50°	234.3
52.5°	161.7
55°	109.9
57.5°	66.3
60°	33.9
62.5°	10.6
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)