

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781386

Luminaire Tested: LER4D40BD010-EC4DR6040509035-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D40BD010-EC4DR6040509035-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4213.7 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781386

CATALOG NUMBER: LER4D40BD010-EC4DR6040509035-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P781386

CATALOG NUMBER: LER4D40BD010-EC4DR6040509035-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	460720
5°	459595
10°	474861
15°	475355
20°	437372
25°	372023
30°	283464
35°	200461
40°	117712
45°	47499
50°	15859
55°	7639
60°	3147
65°	465
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 47499 cd/sqm



TEST NUMBER: P781386

CATALOG NUMBER: LER4D40BD010-EC4DR6040509035-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	404.2	9.6
10°-20°	1164.2	27.6
20°-30°	1393.4	33.1
30°-40°	932.0	22.1
40°-50°	276.3	6.6
50°-60°	39.7	0.9
60°-70°	3.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2961.8	70.3
0°-40°	3893.8	92.4
0°-60°	4209.9	99.9
0°-90°	4213.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4213.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4217	
5°	4190	404
15°	4202	1164
25°	3086	1393
35°	1503	932
45°	307	276
55°	40	40
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781386

CATALOG NUMBER: LER4D40BD010-EC4DR6040509035-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4216.7
2.5°	4211.4
5°	4190.4
7.5°	4247.2
10°	4280.1
12.5°	4274.2
15°	4202.4
17.5°	4033.1
20°	3761.6
22.5°	3435.7
25°	3085.9
27.5°	2691.8
30°	2246.8
32.5°	1849.7
35°	1502.9
37.5°	1155.4
40°	825.3
42.5°	544.2
45°	307.4
47.5°	157.3
50°	93.3
52.5°	60.4
55°	40.1
57.5°	25.7
60°	14.4
62.5°	6.0
65°	1.8
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)