

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781410

Luminaire Tested: LER4D40BD010-EC4DR6540509035-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P781410
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D40BD010-EC4DR6540509035-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3681.7 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781410

CATALOG NUMBER: LER4D40BD010-EC4DR6540509035-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P781410

CATALOG NUMBER: LER4D40BD010-EC4DR6540509035-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195238
5°	194747
10°	194579
15°	188582
20°	171683
25°	149607
30°	124432
35°	98598
40°	71163
45°	44957
50°	23433
55°	12453
60°	6541
65°	3593
70°	1503
75°	1670
80°	1144
85°	1005

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 44957 cd/sqm



TEST NUMBER: P781410

CATALOG NUMBER: LER4D40BD010-EC4DR6540509035-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	316.1	8.6
10°-20°	865.7	23.5
20°-30°	1058.2	28.7
30°-40°	858.6	23.3
40°-50°	427.8	11.6
50°-60°	119.3	3.2
60°-70°	27.1	0.7
70°-80°	7.1	0.2
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2240.0	60.8
0°-40°	3098.6	84.2
0°-60°	3645.7	99.0
0°-90°	3681.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3681.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3343	
5°	3322	316
15°	3119	866
25°	2322	1058
35°	1383	859
45°	544	428
55°	122	119
65°	26	27
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P781410

CATALOG NUMBER: LER4D40BD010-EC4DR6540509035-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3342.9
2.5°	3340.5
5°	3321.8
7.5°	3311.0
10°	3281.0
12.5°	3220.1
15°	3118.9
17.5°	2960.7
20°	2762.3
22.5°	2548.1
25°	2321.6
27.5°	2079.4
30°	1845.1
32.5°	1613.7
35°	1382.9
37.5°	1152.5
40°	933.4
42.5°	728.0
45°	544.3
47.5°	379.2
50°	257.9
52.5°	177.8
55°	122.3
57.5°	82.5
60°	56.0
62.5°	38.8
65°	26.0
67.5°	13.3
70°	8.8
72.5°	8.4
75°	7.4
77.5°	4.9
80°	3.4
82.5°	2.5
85°	1.5
87.5°	1.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)