

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781263

Luminaire Tested: LER4D40BD010-EC4DR3540509030-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D40BD010-EC4DR3540509030-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3595.5 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781263

CATALOG NUMBER: LER4D40BD010-EC4DR3540509030-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P781263

CATALOG NUMBER: LER4D40BD010-EC4DR3540509030-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1080917
5°	1055520
10°	951309
15°	738370
20°	418792
25°	162931
30°	60786
35°	33319
40°	21780
45°	13258
50°	8431
55°	5962
60°	4370
65°	2379
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13258 cd/sqm



TEST NUMBER: P781263

CATALOG NUMBER: LER4D40BD010-EC4DR3540509030-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	885.1	24.6
10°-20°	1728.1	48.1
20°-30°	704.8	19.6
30°-40°	168.7	4.7
40°-50°	70.3	2.0
50°-60°	29.1	0.8
60°-70°	9.1	0.3
70°-80°	0.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3318.0	92.3
0°-40°	3486.7	97.0
0°-60°	3586.1	99.7
0°-90°	3595.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3595.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9893	
5°	9624	885
15°	6528	1728
25°	1352	705
35°	250	169
45°	86	70
55°	31	29
65°	9	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781263

CATALOG NUMBER: LER4D40BD010-EC4DR3540509030-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9893.0
2.5°	9833.7
5°	9623.8
7.5°	9205.2
10°	8574.5
12.5°	7686.4
15°	6527.6
17.5°	5110.3
20°	3601.8
22.5°	2296.7
25°	1351.5
27.5°	763.9
30°	481.8
32.5°	338.3
35°	249.8
37.5°	193.1
40°	152.7
42.5°	117.6
45°	85.8
47.5°	64.2
50°	49.6
52.5°	39.4
55°	31.3
57.5°	25.4
60°	20.0
62.5°	14.6
65°	9.2
67.5°	3.2
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)