

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781435

Luminaire Tested: LER4D40BD010-EC4DR7040509035-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781435
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D40BD010-EC4DR7040509035-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3835.6 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781435

CATALOG NUMBER: LER4D40BD010-EC4DR7040509035-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P781435

CATALOG NUMBER: LER4D40BD010-EC4DR7040509035-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	330776
5°	329956
10°	329233
15°	329142
20°	325924
25°	306164
30°	272942
35°	217627
40°	144498
45°	86391
50°	44790
55°	23545
60°	8326
65°	129
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 86391 cd/sqm



TEST NUMBER: P781435

CATALOG NUMBER: LER4D40BD010-EC4DR7040509035-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.1	7.5
10°-20°	820.5	21.4
20°-30°	1157.5	30.2
30°-40°	999.2	26.1
40°-50°	447.5	11.7
50°-60°	117.2	3.1
60°-70°	7.6	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2264.1	59.0
0°-40°	3263.4	85.1
0°-60°	3828.0	99.8
0°-90°	3835.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3835.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3027	
5°	3008	286
15°	2910	821
25°	2540	1158
35°	1632	999
45°	559	447
55°	124	117
65°	0	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781435

CATALOG NUMBER: LER4D40BD010-EC4DR7040509035-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3027.4
2.5°	3024.1
5°	3008.4
7.5°	2995.3
10°	2967.5
12.5°	2942.5
15°	2909.8
17.5°	2872.3
20°	2803.1
22.5°	2689.3
25°	2539.6
27.5°	2366.0
30°	2163.4
32.5°	1915.7
35°	1631.6
37.5°	1318.0
40°	1013.1
42.5°	769.8
45°	559.1
47.5°	385.4
50°	263.5
52.5°	181.8
55°	123.6
57.5°	74.6
60°	38.1
62.5°	12.0
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)