

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781274

Luminaire Tested: LER4D40BD010-EC4DR3540509050-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781274
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D40BD010-EC4DR3540509050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4230.9 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781274

CATALOG NUMBER: LER4D40BD010-EC4DR3540509050-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P781274

CATALOG NUMBER: LER4D40BD010-EC4DR3540509050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96		
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88		
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84		
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81		
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78		
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75		
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72		
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70		
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1271948
5°	1242061
10°	1119426
15°	868859
20°	492799
25°	191720
30°	71522
35°	39201
40°	25631
45°	15591
50°	9927
55°	7010
60°	5135
65°	2792
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15591 cd/sqm



TEST NUMBER: P781274

CATALOG NUMBER: LER4D40BD010-EC4DR3540509050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1041.5	24.6
10°-20°	2033.5	48.1
20°-30°	829.3	19.6
30°-40°	198.5	4.7
40°-50°	82.7	2.0
50°-60°	34.2	0.8
60°-70°	10.7	0.3
70°-80°	0.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3904.4	92.3
0°-40°	4102.9	97.0
0°-60°	4219.8	99.7
0°-90°	4230.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4230.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11641	
5°	11325	###
15°	7681	2034
25°	1590	829
35°	294	198
45°	101	83
55°	37	34
65°	11	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781274

CATALOG NUMBER: LER4D40BD010-EC4DR3540509050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	11641.4
2.5°	11571.6
5°	11324.6
7.5°	10832.0
10°	10089.8
12.5°	9044.9
15°	7681.2
17.5°	6013.4
20°	4238.3
22.5°	2702.6
25°	1590.3
27.5°	899.0
30°	566.9
32.5°	398.1
35°	293.9
37.5°	227.3
40°	179.7
42.5°	138.4
45°	100.9
47.5°	75.5
50°	58.4
52.5°	46.3
55°	36.8
57.5°	29.8
60°	23.5
62.5°	17.1
65°	10.8
67.5°	3.8
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)