

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781309

Luminaire Tested: LER4D40BD010-EC4DR4540509030-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781309
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D40BD010-EC4DR4540509030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4055.8 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781309

CATALOG NUMBER: LER4D40BD010-EC4DR4540509030-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781309

CATALOG NUMBER: LER4D40BD010-EC4DR4540509030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95			
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77			
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73			
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69			
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66			
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63			
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	783258
5°	760958
10°	728029
15°	666304
20°	528611
25°	330022
30°	181890
35°	81670
40°	32163
45°	15158
50°	7190
55°	3753
60°	1857
65°	440
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15158 cd/sqm



TEST NUMBER: P781309

CATALOG NUMBER: LER4D40BD010-EC4DR4540509030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	651.9	16.1
10°-20°	1604.4	39.6
20°-30°	1270.5	31.3
30°-40°	423.1	10.4
40°-50°	84.0	2.1
50°-60°	19.1	0.5
60°-70°	2.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3526.8	87.0
0°-40°	3949.9	97.4
0°-60°	4053.0	99.9
0°-90°	4055.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4055.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7169	
5°	6938	652
15°	5890	1604
25°	2738	1271
35°	612	423
45°	98	84
55°	20	19
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781309

CATALOG NUMBER: LER4D40BD010-EC4DR4540509030-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7168.7
2.5°	7121.9
5°	6938.1
7.5°	6786.4
10°	6562.0
12.5°	6263.2
15°	5890.5
17.5°	5330.0
20°	4546.3
22.5°	3612.5
25°	2737.5
27.5°	2004.5
30°	1441.7
32.5°	980.5
35°	612.3
37.5°	363.1
40°	225.5
42.5°	148.3
45°	98.1
47.5°	63.2
50°	42.3
52.5°	28.2
55°	19.7
57.5°	13.0
60°	8.5
62.5°	4.5
65°	1.7
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)