

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781339

Luminaire Tested: LER4D40BD010-EC4DR5040509035-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781339
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D40BD010-EC4DR5040509035-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3943.4 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781339

CATALOG NUMBER: LER4D40BD010-EC4DR5040509035-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P781339

CATALOG NUMBER: LER4D40BD010-EC4DR5040509035-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107	112	110	108	106		106	104	102		102	101	99		98	97	97
2	109	105	101	98	107	103	100	97		100	98	95		97	95	93		95	93	91
3	105	99	95	91	103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85	99	93	88	85		90	87	84		89	85	83		87	84	82
5	96	89	84	80	95	88	83	79		86	82	79		85	81	78		83	80	77
6	92	84	79	75	91	83	79	75		82	78	74		81	77	74		79	76	74
7	88	80	75	71	87	79	74	71		78	74	71		77	73	70		76	73	70
8	85	76	71	67	84	76	71	67		75	70	67		74	70	67		73	69	66
9	81	73	68	64	80	72	67	64		71	67	64		71	67	64		70	66	63
10	78	70	64	61	77	69	64	61		68	64	61		68	64	61		67	63	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	694221
5°	686947
10°	675630
15°	615221
20°	511938
25°	363392
30°	192349
35°	78389
40°	29111
45°	13319
50°	5456
55°	2857
60°	1399
65°	414
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13319 cd/sqm



TEST NUMBER: P781339

CATALOG NUMBER: LER4D40BD010-EC4DR5040509035-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	592.0	15.0
10°-20°	1496.1	37.9
20°-30°	1343.9	34.1
30°-40°	420.8	10.7
40°-50°	73.7	1.9
50°-60°	14.7	0.4
60°-70°	2.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3432.1	87.0
0°-40°	3852.9	97.7
0°-60°	3941.2	99.9
0°-90°	3943.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3943.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6354	
5°	6263	592
15°	5439	1496
25°	3014	1344
35°	588	421
45°	86	74
55°	15	15
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781339

CATALOG NUMBER: LER4D40BD010-EC4DR5040509035-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6353.8
2.5°	6322.2
5°	6263.3
7.5°	6173.3
10°	6089.7
12.5°	5821.9
15°	5438.9
17.5°	4952.5
20°	4402.9
22.5°	3767.0
25°	3014.3
27.5°	2216.2
30°	1524.6
32.5°	992.6
35°	587.7
37.5°	337.5
40°	204.1
42.5°	132.9
45°	86.2
47.5°	52.5
50°	32.1
52.5°	22.0
55°	15.0
57.5°	10.2
60°	6.4
62.5°	3.7
65°	1.6
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)