

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781578

Luminaire Tested: LER4D45BD010-EC4DR5040509035-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781578
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D45BD010-EC4DR5040509035-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4774.4 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781578

CATALOG NUMBER: LER4D45BD010-EC4DR5040509035-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P781578

CATALOG NUMBER: LER4D45BD010-EC4DR5040509035-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	109	107	112	110	108	106		106	104	102			102	101	99			95
2	109	105	101	98	107	103	100	97		100	98	95			97	95	93			90
3	105	99	95	91	103	98	94	90		95	92	89			93	90	88			85
4	100	94	89	85	99	93	88	85		90	87	84			89	85	83			80
5	96	89	84	80	95	88	83	79		86	82	79			85	81	78			76
6	92	84	79	75	91	83	79	75		82	78	74			81	77	74			72
7	88	80	75	71	87	79	74	71		78	74	71			77	73	70			69
8	85	76	71	67	84	76	71	67		75	70	67			74	70	67			65
9	81	73	68	64	80	72	67	64		71	67	64			71	67	64			62
10	78	70	64	61	77	69	64	61		68	64	61			68	64	61			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	840532
5°	831722
10°	818018
15°	744874
20°	619816
25°	439981
30°	232885
35°	94902
40°	35244
45°	16132
50°	6612
55°	3467
60°	1704
65°	491
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16132 cd/sqm



TEST NUMBER: P781578

CATALOG NUMBER: LER4D45BD010-EC4DR5040509035-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	716.8	15.0
10°-20°	1811.4	37.9
20°-30°	1627.2	34.1
30°-40°	509.4	10.7
40°-50°	89.2	1.9
50°-60°	17.8	0.4
60°-70°	2.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4155.4	87.0
0°-40°	4664.8	97.7
0°-60°	4771.8	99.9
0°-90°	4774.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4774.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7693	
5°	7583	717
15°	6585	1811
25°	3650	1627
35°	712	509
45°	104	89
55°	18	18
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781578

CATALOG NUMBER: LER4D45BD010-EC4DR5040509035-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7692.9
2.5°	7654.6
5°	7583.3
7.5°	7474.3
10°	7373.1
12.5°	7048.8
15°	6585.1
17.5°	5996.2
20°	5330.7
22.5°	4560.9
25°	3649.6
27.5°	2683.2
30°	1845.9
32.5°	1201.8
35°	711.5
37.5°	408.6
40°	247.1
42.5°	160.8
45°	104.4
47.5°	63.6
50°	38.9
52.5°	26.6
55°	18.2
57.5°	12.3
60°	7.8
62.5°	4.5
65°	1.9
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)