

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781593

Luminaire Tested: LER4D45BD010-EC4DR5540509027-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D45BD010-EC4DR5540509027-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4305.4 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781593

CATALOG NUMBER: LER4D45BD010-EC4DR5540509027-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781593

CATALOG NUMBER: LER4D45BD010-EC4DR5540509027-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65		
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61		
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57		
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54		
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	527500
5°	506548
10°	504639
15°	490139
20°	439477
25°	363211
30°	274355
35°	198927
40°	127311
45°	58145
50°	19021
55°	8210
60°	3540
65°	465
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 58145 cd/sqm



TEST NUMBER: P781593

CATALOG NUMBER: LER4D45BD010-EC4DR5540509027-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.5	10.2
10°-20°	1199.4	27.9
20°-30°	1366.8	31.7
30°-40°	930.5	21.6
40°-50°	320.6	7.4
50°-60°	44.3	1.0
60°-70°	4.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3005.7	69.8
0°-40°	3936.2	91.4
0°-60°	4301.2	99.9
0°-90°	4305.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4305.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4828	
5°	4618	439
15°	4333	1199
25°	3013	1367
35°	1491	930
45°	376	321
55°	43	44
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781593

CATALOG NUMBER: LER4D45BD010-EC4DR5540509027-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4827.9
2.5°	4717.2
5°	4618.5
7.5°	4570.0
10°	4548.5
12.5°	4476.7
15°	4333.1
17.5°	4105.2
20°	3779.7
22.5°	3404.0
25°	3012.8
27.5°	2605.4
30°	2174.6
32.5°	1809.7
35°	1491.4
37.5°	1188.7
40°	892.6
42.5°	618.6
45°	376.3
47.5°	202.8
50°	111.9
52.5°	66.4
55°	43.1
57.5°	27.5
60°	16.2
62.5°	7.2
65°	1.8
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)