

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781402

Luminaire Tested: LER4D40BD010-EC4DR6540509027-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P781402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D40BD010-EC4DR6540509027-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3536.5 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781402

CATALOG NUMBER: LER4D40BD010-EC4DR6540509027-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P781402

CATALOG NUMBER: LER4D40BD010-EC4DR6540509027-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187535
5°	187067
10°	186905
15°	181145
20°	164908
25°	143705
30°	119522
35°	94705
40°	68350
45°	43181
50°	22506
55°	11964
60°	6284
65°	3455
70°	1451
75°	1602
80°	1110
85°	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43181 cd/sqm



TEST NUMBER: P781402

CATALOG NUMBER: LER4D40BD010-EC4DR6540509027-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	303.7	8.6
10°-20°	831.5	23.5
20°-30°	1016.4	28.7
30°-40°	824.7	23.3
40°-50°	411.0	11.6
50°-60°	114.6	3.2
60°-70°	26.0	0.7
70°-80°	6.8	0.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2151.6	60.8
0°-40°	2976.3	84.2
0°-60°	3501.9	99.0
0°-90°	3536.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3536.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3211	
5°	3191	304
15°	2996	832
25°	2230	1016
35°	1328	825
45°	523	411
55°	118	115
65°	25	26
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P781402

CATALOG NUMBER: LER4D40BD010-EC4DR6540509027-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3211.0
2.5°	3208.7
5°	3190.8
7.5°	3180.4
10°	3151.6
12.5°	3093.1
15°	2995.9
17.5°	2843.9
20°	2653.3
22.5°	2447.6
25°	2230.0
27.5°	1997.4
30°	1772.3
32.5°	1550.1
35°	1328.3
37.5°	1107.0
40°	896.5
42.5°	699.3
45°	522.8
47.5°	364.3
50°	247.7
52.5°	170.8
55°	117.5
57.5°	79.3
60°	53.8
62.5°	37.3
65°	25.0
67.5°	12.7
70°	8.5
72.5°	8.0
75°	7.1
77.5°	4.7
80°	3.3
82.5°	2.4
85°	1.4
87.5°	0.9
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)