

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781640

Luminaire Tested: LER4D45BD010-EC4DR6540509027-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P781640
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D45BD010-EC4DR6540509027-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3425.5 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781640

CATALOG NUMBER: LER4D45BD010-EC4DR6540509027-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P781640

CATALOG NUMBER: LER4D45BD010-EC4DR6540509027-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181648
5°	181192
10°	181034
15°	175455
20°	159731
25°	139194
30°	115772
35°	91732
40°	66208
45°	41826
50°	21806
55°	11588
60°	6086
65°	3344
70°	1400
75°	1557
80°	1076
85°	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 41826 cd/sqm



TEST NUMBER: P781640

CATALOG NUMBER: LER4D45BD010-EC4DR6540509027-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.1	8.6
10°-20°	805.4	23.5
20°-30°	984.5	28.7
30°-40°	798.8	23.3
40°-50°	398.0	11.6
50°-60°	111.0	3.2
60°-70°	25.2	0.7
70°-80°	6.6	0.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2084.1	60.8
0°-40°	2882.9	84.2
0°-60°	3392.0	99.0
0°-90°	3425.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3425.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3110	
5°	3091	294
15°	2902	805
25°	2160	985
35°	1287	799
45°	506	398
55°	114	111
65°	24	25
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P781640

CATALOG NUMBER: LER4D45BD010-EC4DR6540509027-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3110.2
2.5°	3107.9
5°	3090.6
7.5°	3080.5
10°	3052.6
12.5°	2996.0
15°	2901.8
17.5°	2754.6
20°	2570.0
22.5°	2370.7
25°	2160.0
27.5°	1934.7
30°	1716.7
32.5°	1501.4
35°	1286.6
37.5°	1072.2
40°	868.4
42.5°	677.3
45°	506.4
47.5°	352.8
50°	240.0
52.5°	165.5
55°	113.8
57.5°	76.8
60°	52.1
62.5°	36.1
65°	24.2
67.5°	12.3
70°	8.2
72.5°	7.8
75°	6.9
77.5°	4.6
80°	3.2
82.5°	2.3
85°	1.4
87.5°	0.9
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)