

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781411

Luminaire Tested: LER4D40BD010-EC4DR6540509035-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P781411
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D40BD010-EC4DR6540509035-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3331.9 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781411

CATALOG NUMBER: LER4D40BD010-EC4DR6540509035-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P781411

CATALOG NUMBER: LER4D40BD010-EC4DR6540509035-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176689
5°	176244
10°	176094
15°	170660
20°	155368
25°	135392
30°	112610
35°	89229
40°	64401
45°	40687
50°	21207
55°	11272
60°	5922
65°	3261
70°	1366
75°	1512
80°	1043
85°	871

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 40687 cd/sqm



TEST NUMBER: P781411

CATALOG NUMBER: LER4D40BD010-EC4DR6540509035-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.1	8.6
10°-20°	783.4	23.5
20°-30°	957.6	28.7
30°-40°	777.0	23.3
40°-50°	387.2	11.6
50°-60°	108.0	3.2
60°-70°	24.5	0.7
70°-80°	6.4	0.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2027.2	60.8
0°-40°	2804.2	84.2
0°-60°	3299.3	99.0
0°-90°	3331.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3331.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3025	
5°	3006	286
15°	2822	783
25°	2101	958
35°	1252	777
45°	493	387
55°	111	108
65°	24	25
75°	7	6
85°	1	2
90°	0	



TEST NUMBER: P781411

CATALOG NUMBER: LER4D40BD010-EC4DR6540509035-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3025.3
2.5°	3023.0
5°	3006.2
7.5°	2996.4
10°	2969.3
12.5°	2914.1
15°	2822.5
17.5°	2679.4
20°	2499.8
22.5°	2306.0
25°	2101.0
27.5°	1881.8
30°	1669.8
32.5°	1460.4
35°	1251.5
37.5°	1043.0
40°	844.7
42.5°	658.8
45°	492.6
47.5°	343.2
50°	233.4
52.5°	160.9
55°	110.7
57.5°	74.7
60°	50.7
62.5°	35.1
65°	23.6
67.5°	12.0
70°	8.0
72.5°	7.6
75°	6.7
77.5°	4.4
80°	3.1
82.5°	2.2
85°	1.3
87.5°	0.9
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report







(END OF REPORT)