

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781658

Luminaire Tested: LER4D45BD010-EC4DR6540509050-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P781658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D45BD010-EC4DR6540509050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4251.6 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781658

CATALOG NUMBER: LER4D45BD010-EC4DR6540509050-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P781658

CATALOG NUMBER: LER4D45BD010-EC4DR6540509050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225462
5°	224893
10°	224700
15°	217774
20°	198259
25°	172768
30°	143692
35°	113856
40°	82172
45°	51920
50°	27058
55°	14388
60°	7557
65°	4160
70°	1742
75°	1918
80°	1345
85°	1139

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 51920 cd/sqm



TEST NUMBER: P781658

CATALOG NUMBER: LER4D45BD010-EC4DR6540509050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.1	8.6
10°-20°	999.7	23.5
20°-30°	1222.0	28.7
30°-40°	991.5	23.3
40°-50°	494.1	11.6
50°-60°	137.8	3.2
60°-70°	31.3	0.7
70°-80°	8.1	0.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2586.7	60.8
0°-40°	3578.2	84.2
0°-60°	4210.1	99.0
0°-90°	4251.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4251.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3860	
5°	3836	365
15°	3602	1000
25°	2681	1222
35°	1597	991
45°	629	494
55°	141	138
65°	30	31
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P781658

CATALOG NUMBER: LER4D45BD010-EC4DR6540509050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3860.4
2.5°	3857.6
5°	3836.0
7.5°	3823.5
10°	3788.9
12.5°	3718.6
15°	3601.7
17.5°	3419.0
20°	3189.9
22.5°	2942.5
25°	2681.0
27.5°	2401.3
30°	2130.7
32.5°	1863.5
35°	1596.9
37.5°	1330.9
40°	1077.8
42.5°	840.7
45°	628.6
47.5°	437.9
50°	297.8
52.5°	205.4
55°	141.3
57.5°	95.3
60°	64.7
62.5°	44.8
65°	30.1
67.5°	15.3
70°	10.2
72.5°	9.6
75°	8.5
77.5°	5.7
80°	4.0
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)