

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781665

Luminaire Tested: LER4D45BD010-EC4DR7040509027-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781665
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D45BD010-EC4DR7040509027-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4250.1 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781665

CATALOG NUMBER: LER4D45BD010-EC4DR7040509027-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781665

CATALOG NUMBER: LER4D45BD010-EC4DR7040509027-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	366515
5°	365601
10°	364814
15°	364706
20°	361144
25°	339244
30°	302439
35°	241143
40°	160116
45°	95724
50°	49634
55°	26078
60°	9222
65°	155
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 95724 cd/sqm



TEST NUMBER: P781665

CATALOG NUMBER: LER4D45BD010-EC4DR7040509027-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	317.0	7.5
10°-20°	909.2	21.4
20°-30°	1282.6	30.2
30°-40°	1107.2	26.1
40°-50°	495.8	11.7
50°-60°	129.8	3.1
60°-70°	8.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2508.8	59.0
0°-40°	3616.0	85.1
0°-60°	4241.6	99.8
0°-90°	4250.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4250.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3354	
5°	3333	317
15°	3224	909
25°	2814	1283
35°	1808	1107
45°	620	496
55°	137	130
65°	1	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781665

CATALOG NUMBER: LER4D45BD010-EC4DR7040509027-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3354.5
2.5°	3350.9
5°	3333.4
7.5°	3318.9
10°	3288.2
12.5°	3260.4
15°	3224.2
17.5°	3182.6
20°	3106.0
22.5°	2979.9
25°	2814.0
27.5°	2621.6
30°	2397.2
32.5°	2122.7
35°	1807.9
37.5°	1460.4
40°	1122.6
42.5°	853.0
45°	619.5
47.5°	427.1
50°	292.0
52.5°	201.5
55°	136.9
57.5°	82.6
60°	42.2
62.5°	13.3
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)