

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781517

Luminaire Tested: LER4D45BD010-EC4DR4040509024-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781517
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D45BD010-EC4DR4040509024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3880.2 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781517

CATALOG NUMBER: LER4D45BD010-EC4DR4040509024-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781517

CATALOG NUMBER: LER4D45BD010-EC4DR4040509024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96			
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92			
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88			
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84			
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81			
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77			
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74			
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72			
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69			
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	987073
5°	982277
10°	928465
15°	789317
20°	537971
25°	224463
30°	70576
35°	32799
40°	18143
45°	8313
50°	4029
55°	2210
60°	1158
65°	414
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8313 cd/sqm



TEST NUMBER: P781517

CATALOG NUMBER: LER4D45BD010-EC4DR4040509024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	836.3	21.6
10°-20°	1873.5	48.3
20°-30°	937.8	24.2
30°-40°	171.9	4.4
40°-50°	47.4	1.2
50°-60°	11.1	0.3
60°-70°	2.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3647.5	94.0
0°-40°	3819.4	98.4
0°-60°	3878.0	99.9
0°-90°	3880.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3880.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9034	
5°	8956	836
15°	6978	1873
25°	1862	938
35°	246	172
45°	54	47
55°	12	11
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781517

CATALOG NUMBER: LER4D45BD010-EC4DR4040509024-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9034.1
2.5°	9020.9
5°	8956.0
7.5°	8749.1
10°	8368.6
12.5°	7775.4
15°	6978.0
17.5°	5941.0
20°	4626.8
22.5°	3154.4
25°	1861.9
27.5°	984.3
30°	559.4
32.5°	361.5
35°	245.9
37.5°	175.7
40°	127.2
42.5°	87.1
45°	53.8
47.5°	34.3
50°	23.7
52.5°	16.9
55°	11.6
57.5°	7.4
60°	5.3
62.5°	3.2
65°	1.6
67.5°	1.1
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)