

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781735

Luminaire Tested: LER4D50D010-EC4DR3540509024-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR3540509024-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3963.5 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781735

CATALOG NUMBER: LER4D50D010-EC4DR3540509024-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P781735

CATALOG NUMBER: LER4D50D010-EC4DR3540509024-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1191532
5°	1163531
10°	1048653
15°	813919
20°	461650
25°	179604
30°	67005
35°	36734
40°	24005
45°	14617
50°	9298
55°	6572
60°	4807
65°	2611
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14617 cd/sqm



TEST NUMBER: P781735

CATALOG NUMBER: LER4D50D010-EC4DR3540509024-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	975.7	24.6
10°-20°	1905.0	48.1
20°-30°	776.9	19.6
30°-40°	185.9	4.7
40°-50°	77.5	2.0
50°-60°	32.1	0.8
60°-70°	10.1	0.3
70°-80°	0.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3657.5	92.3
0°-40°	3843.5	97.0
0°-60°	3953.0	99.7
0°-90°	3963.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3963.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10905	
5°	10609	976
15°	7196	1905
25°	1490	777
35°	275	186
45°	95	77
55°	34	32
65°	10	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781735

CATALOG NUMBER: LER4D50D010-EC4DR3540509024-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	10905.4
2.5°	10840.0
5°	10608.6
7.5°	10147.1
10°	9451.9
12.5°	8473.0
15°	7195.5
17.5°	5633.2
20°	3970.4
22.5°	2531.7
25°	1489.8
27.5°	842.1
30°	531.1
32.5°	372.9
35°	275.4
37.5°	212.9
40°	168.3
42.5°	129.6
45°	94.6
47.5°	70.8
50°	54.7
52.5°	43.4
55°	34.5
57.5°	28.0
60°	22.0
62.5°	16.1
65°	10.1
67.5°	3.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)