

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781737

Luminaire Tested: LER4D50D010-EC4DR3540509027-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR3540509027-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4723.0 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781737

CATALOG NUMBER: LER4D50D010-EC4DR3540509027-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781737

CATALOG NUMBER: LER4D50D010-EC4DR3540509027-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96			
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92			
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88			
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84			
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81			
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78			
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75			
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72			
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70			
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1419887
5°	1386518
10°	1249621
15°	969905
20°	550122
25°	214023
30°	79849
35°	43763
40°	28612
45°	17414
50°	11083
55°	7829
60°	5725
65°	3102
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17414 cd/sqm

TEST NUMBER: P781737

CATALOG NUMBER: LER4D50D010-EC4DR3540509027-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1162.7	24.6
10°-20°	2270.0	48.1
20°-30°	925.8	19.6
30°-40°	221.6	4.7
40°-50°	92.3	2.0
50°-60°	38.2	0.8
60°-70°	12.0	0.3
70°-80°	0.3	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4358.5	92.3
0°-40°	4580.1	97.0
0°-60°	4710.6	99.7
0°-90°	4723.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4723.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12995	
5°	12642	###
15°	8574	2270
25°	1775	926
35°	328	222
45°	113	92
55°	41	38
65°	12	12
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781737

CATALOG NUMBER: LER4D50D010-EC4DR3540509027-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	12995.4
2.5°	12917.4
5°	12641.7
7.5°	12091.8
10°	11263.3
12.5°	10096.8
15°	8574.5
17.5°	6712.8
20°	4731.3
22.5°	3016.9
25°	1775.3
27.5°	1003.5
30°	632.9
32.5°	444.4
35°	328.1
37.5°	253.7
40°	200.6
42.5°	154.5
45°	112.7
47.5°	84.3
50°	65.2
52.5°	51.7
55°	41.1
57.5°	33.3
60°	26.2
62.5°	19.1
65°	12.0
67.5°	4.3
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)