

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781621

Luminaire Tested: LER4D45BD010-EC4DR6040509030-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D45BD010-EC4DR6040509030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4350.0 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781621

CATALOG NUMBER: LER4D45BD010-EC4DR6040509030-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781621

CATALOG NUMBER: LER4D45BD010-EC4DR6040509030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	475634
5°	474468
10°	490227
15°	490738
20°	451522
25°	384055
30°	292636
35°	206943
40°	121521
45°	49029
50°	16369
55°	7886
60°	3234
65°	491
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 49029 cd/sqm



TEST NUMBER: P781621

CATALOG NUMBER: LER4D45BD010-EC4DR6040509030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	417.3	9.6
10°-20°	1201.9	27.6
20°-30°	1438.5	33.1
30°-40°	962.1	22.1
40°-50°	285.3	6.6
50°-60°	41.0	0.9
60°-70°	3.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3057.7	70.3
0°-40°	4019.8	92.4
0°-60°	4346.1	99.9
0°-90°	4350.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4350.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4353	
5°	4326	417
15°	4338	1202
25°	3186	1438
35°	1552	962
45°	317	285
55°	41	41
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781621

CATALOG NUMBER: LER4D45BD010-EC4DR6040509030-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4353.2
2.5°	4347.6
5°	4326.0
7.5°	4384.7
10°	4418.6
12.5°	4412.4
15°	4338.4
17.5°	4163.6
20°	3883.3
22.5°	3546.9
25°	3185.7
27.5°	2778.8
30°	2319.5
32.5°	1909.6
35°	1551.5
37.5°	1192.8
40°	852.0
42.5°	561.8
45°	317.3
47.5°	162.4
50°	96.3
52.5°	62.4
55°	41.4
57.5°	26.5
60°	14.8
62.5°	6.2
65°	1.9
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)