

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781812

Luminaire Tested: LER4D50D010-EC4DR5040509030-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR5040509030-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5000.4 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781812

CATALOG NUMBER: LER4D50D010-EC4DR5040509030-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P781812

CATALOG NUMBER: LER4D50D010-EC4DR5040509030-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	109	107	112	110	108	106		106	104	102			102	101	99			95
2	109	105	101	98	107	103	100	97		100	98	95			97	95	93			90
3	105	99	95	91	103	98	94	90		95	92	89			93	90	88			85
4	100	94	89	85	99	93	88	85		90	87	84			89	85	83			80
5	96	89	84	80	95	88	83	79		86	82	79			85	81	78			76
6	92	84	79	75	91	83	79	75		82	78	74			81	77	74			72
7	88	80	75	71	87	79	74	71		78	74	71			77	73	70			69
8	85	76	71	67	84	76	71	67		75	70	67			74	70	67			65
9	81	73	68	64	80	72	67	64		71	67	64			71	67	64			62
10	78	70	64	61	77	69	64	61		68	64	61			68	64	61			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	880303
5°	871075
10°	856727
15°	780121
20°	649140
25°	460801
30°	243899
35°	99397
40°	36913
45°	16904
50°	6935
55°	3619
60°	1792
65°	517
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16904 cd/sqm

TEST NUMBER: P781812

CATALOG NUMBER: LER4D50D010-EC4DR5040509030-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	750.7	15.0
10°-20°	1897.1	37.9
20°-30°	1704.1	34.1
30°-40°	533.6	10.7
40°-50°	93.5	1.9
50°-60°	18.6	0.4
60°-70°	2.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4352.0	87.0
0°-40°	4885.5	97.7
0°-60°	4997.6	99.9
0°-90°	5000.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5000.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8057	
5°	7942	751
15°	6897	1897
25°	3822	1704
35°	745	534
45°	109	93
55°	19	19
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781812

CATALOG NUMBER: LER4D50D010-EC4DR5040509030-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	8056.9
2.5°	8016.8
5°	7942.1
7.5°	7827.9
10°	7722.0
12.5°	7382.3
15°	6896.7
17.5°	6279.9
20°	5582.9
22.5°	4776.6
25°	3822.3
27.5°	2810.2
30°	1933.2
32.5°	1258.7
35°	745.2
37.5°	427.9
40°	258.8
42.5°	168.5
45°	109.4
47.5°	66.6
50°	40.8
52.5°	27.9
55°	19.0
57.5°	12.9
60°	8.2
62.5°	4.8
65°	2.0
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)