

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781630

Luminaire Tested: LER4D45BD010-EC4DR6040509040-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781630
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D45BD010-EC4DR6040509040-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4831.4 lumens
Efficiency: N/A
Efficacy: 124.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781630

CATALOG NUMBER: LER4D45BD010-EC4DR6040509040-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P781630

CATALOG NUMBER: LER4D45BD010-EC4DR6040509040-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	87	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	63		82	73	67	63		72	67	63		71	66	63		69	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	61	58
9	75	65	59	55		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	55	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	528265
5°	526981
10°	544480
15°	545045
20°	501496
25°	426563
30°	325022
35°	229845
40°	134971
45°	54468
50°	18188
55°	8744
60°	3606
65°	543
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 54468 cd/sqm

TEST NUMBER: P781630

CATALOG NUMBER: LER4D45BD010-EC4DR6040509040-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	463.5	9.6
10°-20°	1334.9	27.6
20°-30°	1597.7	33.1
30°-40°	1068.6	22.1
40°-50°	316.8	6.6
50°-60°	45.6	0.9
60°-70°	4.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3396.1	70.3
0°-40°	4464.7	92.4
0°-60°	4827.1	99.9
0°-90°	4831.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4831.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4835	
5°	4805	463
15°	4818	1335
25°	3538	1598
35°	1723	1069
45°	352	317
55°	46	46
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781630

CATALOG NUMBER: LER4D45BD010-EC4DR6040509040-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4834.9
2.5°	4828.8
5°	4804.8
7.5°	4869.9
10°	4907.6
12.5°	4900.8
15°	4818.5
17.5°	4624.4
20°	4313.1
22.5°	3939.4
25°	3538.3
27.5°	3086.4
30°	2576.2
32.5°	2120.9
35°	1723.2
37.5°	1324.8
40°	946.3
42.5°	624.0
45°	352.5
47.5°	180.3
50°	107.0
52.5°	69.3
55°	45.9
57.5°	29.5
60°	16.5
62.5°	6.9
65°	2.1
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)