

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781817

Luminaire Tested: LER4D50D010-EC4DR5040509035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781817
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR5040509035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5340.1 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781817

CATALOG NUMBER: LER4D50D010-EC4DR5040509035-4LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P781817

CATALOG NUMBER: LER4D50D010-EC4DR5040509035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	109	107	112	110	108	106		106	104	102			102	101	99			98
2	109	105	101	98	107	103	100	97		100	98	95			97	95	93			95
3	105	99	95	91	103	98	94	90		95	92	89			93	90	88			91
4	100	94	89	85	99	93	88	85		90	87	84			89	85	83			87
5	96	89	84	80	95	88	83	79		86	82	79			85	81	78			83
6	92	84	79	75	91	83	79	75		82	78	74			81	77	74			79
7	88	80	75	71	87	79	74	71		78	74	71			77	73	70			76
8	85	76	71	67	84	76	71	67		75	70	67			74	70	67			73
9	81	73	68	64	80	72	67	64		71	67	64			71	67	64			70
10	78	70	64	61	77	69	64	61		68	64	61			68	64	61			67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	940123
5°	930268
10°	914941
15°	833126
20°	693254
25°	492109
30°	260477
35°	106146
40°	39423
45°	18048
50°	7394
55°	3867
60°	1901
65°	569
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18048 cd/sqm



TEST NUMBER: P781817

CATALOG NUMBER: LER4D50D010-EC4DR5040509035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	801.7	15.0
10°-20°	2026.1	37.9
20°-30°	1819.9	34.1
30°-40°	569.8	10.7
40°-50°	99.8	1.9
50°-60°	19.9	0.4
60°-70°	3.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4647.7	87.0
0°-40°	5217.5	97.7
0°-60°	5337.1	99.9
0°-90°	5340.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5340.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8604	
5°	8482	802
15°	7365	2026
25°	4082	1820
35°	796	570
45°	117	100
55°	20	20
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781817

CATALOG NUMBER: LER4D50D010-EC4DR5040509035-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	8604.4
2.5°	8561.6
5°	8481.8
7.5°	8359.9
10°	8246.7
12.5°	7884.0
15°	7365.3
17.5°	6706.6
20°	5962.3
22.5°	5101.2
25°	4082.0
27.5°	3001.1
30°	2064.6
32.5°	1344.2
35°	795.8
37.5°	457.0
40°	276.4
42.5°	179.9
45°	116.8
47.5°	71.1
50°	43.5
52.5°	29.7
55°	20.3
57.5°	13.8
60°	8.7
62.5°	5.1
65°	2.2
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)