

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781826

Luminaire Tested: LER4D50D010-EC4DR5040509050-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR5040509050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5911.2 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781826

CATALOG NUMBER: LER4D50D010-EC4DR5040509050-4LBS1LI

Luminous Intensity Polar Plot



TEST NUMBER: P781826

CATALOG NUMBER: LER4D50D010-EC4DR5040509050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	109	107	112	110	108	106		106	104	102			102	101	99			95
2	109	105	101	98	107	103	100	97		100	98	95			97	95	93			90
3	105	99	95	91	103	98	94	90		95	92	89			93	90	88			85
4	100	94	89	85	99	93	88	85		90	87	84			89	85	83			80
5	96	89	84	80	95	88	83	79		86	82	79			85	81	78			76
6	92	84	79	75	91	83	79	75		82	78	74			81	77	74			72
7	88	80	75	71	87	79	74	71		78	74	71			77	73	70			69
8	85	76	71	67	84	76	71	67		75	70	67			74	70	67			65
9	81	73	68	64	80	72	67	64		71	67	64			71	67	64			62
10	78	70	64	61	77	69	64	61		68	64	61			68	64	61			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1040654
5°	1029746
10°	1012784
15°	922227
20°	767389
25°	544732
30°	288334
35°	117497
40°	43630
45°	19979
50°	8193
55°	4286
60°	2098
65°	620
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19979 cd/sqm



TEST NUMBER: P781826

CATALOG NUMBER: LER4D50D010-EC4DR5040509050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	887.4	15.0
10°-20°	2242.7	37.9
20°-30°	2014.6	34.1
30°-40°	630.8	10.7
40°-50°	110.4	1.9
50°-60°	22.0	0.4
60°-70°	3.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5144.7	87.0
0°-40°	5775.5	97.7
0°-60°	5907.9	99.9
0°-90°	5911.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5911.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9524	
5°	9389	887
15°	8153	2243
25°	4518	2015
35°	881	631
45°	129	110
55°	22	22
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781826

CATALOG NUMBER: LER4D50D010-EC4DR5040509050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9524.5
2.5°	9477.1
5°	9388.8
7.5°	9253.9
10°	9128.6
12.5°	8727.1
15°	8153.0
17.5°	7423.8
20°	6599.9
22.5°	5646.8
25°	4518.5
27.5°	3322.1
30°	2285.4
32.5°	1488.0
35°	880.9
37.5°	505.9
40°	305.9
42.5°	199.1
45°	129.3
47.5°	78.7
50°	48.2
52.5°	32.9
55°	22.5
57.5°	15.3
60°	9.6
62.5°	5.6
65°	2.4
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)