

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781839

Luminaire Tested: LER4D50D010-EC4DR5540509030-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR5540509030-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4949.4 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781839

CATALOG NUMBER: LER4D50D010-EC4DR5540509030-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P781839

CATALOG NUMBER: LER4D50D010-EC4DR5540509030-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	606397
5°	582314
10°	580116
15°	563449
20°	505217
25°	417533
30°	315396
35°	228685
40°	146352
45°	66845
50°	21859
55°	9429
60°	4065
65°	543
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 66845 cd/sqm



TEST NUMBER: P781839

CATALOG NUMBER: LER4D50D010-EC4DR5540509030-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	505.2	10.2
10°-20°	1378.8	27.9
20°-30°	1571.3	31.7
30°-40°	1069.7	21.6
40°-50°	368.6	7.4
50°-60°	50.9	1.0
60°-70°	5.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3455.3	69.8
0°-40°	4524.9	91.4
0°-60°	4944.5	99.9
0°-90°	4949.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4949.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5550	
5°	5309	505
15°	4981	1379
25°	3463	1571
35°	1714	1070
45°	433	369
55°	50	51
65°	2	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781839

CATALOG NUMBER: LER4D50D010-EC4DR5540509030-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5550.0
2.5°	5422.8
5°	5309.3
7.5°	5253.6
10°	5228.8
12.5°	5146.3
15°	4981.2
17.5°	4719.2
20°	4345.1
22.5°	3913.2
25°	3463.4
27.5°	2995.1
30°	2499.9
32.5°	2080.4
35°	1714.5
37.5°	1366.5
40°	1026.1
42.5°	711.1
45°	432.6
47.5°	233.1
50°	128.6
52.5°	76.3
55°	49.5
57.5°	31.6
60°	18.6
62.5°	8.3
65°	2.1
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)