

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781866

Luminaire Tested: LER4D50D010-EC4DR6040509035-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781866
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR6040509035-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5420.6 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781866

CATALOG NUMBER: LER4D50D010-EC4DR6040509035-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P781866

CATALOG NUMBER: LER4D50D010-EC4DR6040509035-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	592696
5°	591242
10°	610881
15°	611511
20°	562656
25°	478583
30°	364663
35°	257869
40°	151430
45°	61096
50°	20398
55°	9810
60°	4043
65°	595
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 61096 cd/sqm



TEST NUMBER: P781866

CATALOG NUMBER: LER4D50D010-EC4DR6040509035-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	520.0	9.6
10°-20°	1497.7	27.6
20°-30°	1792.5	33.1
30°-40°	1198.9	22.1
40°-50°	355.5	6.6
50°-60°	51.1	0.9
60°-70°	4.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3810.2	70.3
0°-40°	5009.1	92.4
0°-60°	5415.7	99.9
0°-90°	5420.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5420.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5425	
5°	5391	520
15°	5406	1498
25°	3970	1793
35°	1933	1199
45°	395	355
55°	52	51
65°	2	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781866

CATALOG NUMBER: LER4D50D010-EC4DR6040509035-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5424.6
2.5°	5417.6
5°	5390.7
7.5°	5463.8
10°	5506.1
12.5°	5498.4
15°	5406.1
17.5°	5188.4
20°	4839.1
22.5°	4419.8
25°	3969.8
27.5°	3462.8
30°	2890.4
32.5°	2379.5
35°	1933.3
37.5°	1486.3
40°	1061.7
42.5°	700.1
45°	395.4
47.5°	202.3
50°	120.0
52.5°	77.7
55°	51.5
57.5°	33.1
60°	18.5
62.5°	7.7
65°	2.3
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)