

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781879

Luminaire Tested: LER4D50D010-EC4DR6540509024-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P781879
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR6540509024-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3634.6 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781879

CATALOG NUMBER: LER4D50D010-EC4DR6540509024-4LBS1MW

Luminous Intensity Polar Plot



CATALOG NUMBER: LER4D50D010-EC4DR6540509024-4LBS1MW

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10			
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47			

	0°
0°	192739
5°	192250
10°	192088
15°	186169
20°	169483
25°	147694
30°	122840
35°	97329
40°	70248
45°	44379
50°	23133
55°	12300
60°	6459
65°	3552
70°	1486
75°	1647
80°	1144
85°	1005

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 44379 cd/sqm



TEST NUMBER: P781879

CATALOG NUMBER: LER4D50D010-EC4DR6540509024-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	312.1	8.6
10°-20°	854.6	23.5
20°-30°	1044.6	28.7
30°-40°	847.6	23.3
40°-50°	422.4	11.6
50°-60°	117.8	3.2
60°-70°	26.8	0.7
70°-80°	6.9	0.2
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2211.3	60.8
0°-40°	3058.9	84.2
0°-60°	3599.1	99.0
0°-90°	3634.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3634.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3300	
5°	3279	312
15°	3079	855
25°	2292	1045
35°	1365	848
45°	537	422
55°	121	118
65°	26	27
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P781879

CATALOG NUMBER: LER4D50D010-EC4DR6540509024-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3300.1
2.5°	3297.7
5°	3279.2
7.5°	3268.6
10°	3239.0
12.5°	3178.9
15°	3079.0
17.5°	2922.8
20°	2726.9
22.5°	2515.4
25°	2291.9
27.5°	2052.8
30°	1821.5
32.5°	1593.1
35°	1365.1
37.5°	1137.7
40°	921.4
42.5°	718.7
45°	537.3
47.5°	374.4
50°	254.6
52.5°	175.6
55°	120.8
57.5°	81.5
60°	55.3
62.5°	38.3
65°	25.7
67.5°	13.1
70°	8.7
72.5°	8.2
75°	7.3
77.5°	4.8
80°	3.4
82.5°	2.4
85°	1.5
87.5°	1.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)