

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781910

Luminaire Tested: LER4D50D010-EC4DR7040509030-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781910
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR7040509030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5399.3 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781910

CATALOG NUMBER: LER4D50D010-EC4DR7040509030-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P781910

CATALOG NUMBER: LER4D50D010-EC4DR7040509030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	465615
5°	464454
10°	463456
15°	463319
20°	458789
25°	430975
30°	384218
35°	306340
40°	203404
45°	121606
50°	63045
55°	33145
60°	11713
65°	207
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 121606 cd/sqm



TEST NUMBER: P781910

CATALOG NUMBER: LER4D50D010-EC4DR7040509030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	402.7	7.5
10°-20°	1155.0	21.4
20°-30°	1629.4	30.2
30°-40°	1406.6	26.1
40°-50°	629.9	11.7
50°-60°	164.9	3.1
60°-70°	10.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3187.1	59.0
0°-40°	4593.7	85.1
0°-60°	5388.5	99.8
0°-90°	5399.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5399.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4262	
5°	4235	403
15°	4096	1155
25°	3575	1629
35°	2297	1407
45°	787	630
55°	174	165
65°	1	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781910

CATALOG NUMBER: LER4D50D010-EC4DR7040509030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4261.5
2.5°	4257.0
5°	4234.7
7.5°	4216.3
10°	4177.3
12.5°	4142.0
15°	4096.0
17.5°	4043.1
20°	3945.8
22.5°	3785.7
25°	3574.9
27.5°	3330.5
30°	3045.4
32.5°	2696.7
35°	2296.7
37.5°	1855.3
40°	1426.1
42.5°	1083.6
45°	787.0
47.5°	542.6
50°	370.9
52.5°	256.0
55°	174.0
57.5°	105.0
60°	53.6
62.5°	16.9
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)