

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781917

Luminaire Tested: LER4D50D010-EC4DR7040509040-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781917
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR7040509040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5439.2 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781917

CATALOG NUMBER: LER4D50D010-EC4DR7040509040-4LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P781917

CATALOG NUMBER: LER4D50D010-EC4DR7040509040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56		
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	469067
5°	467898
10°	466884
15°	466758
20°	462185
25°	434170
30°	387057
35°	308608
40°	204916
45°	122502
50°	63521
55°	33374
60°	11800
65°	207
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 122502 cd/sqm



TEST NUMBER: P781917

CATALOG NUMBER: LER4D50D010-EC4DR7040509040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	405.7	7.5
10°-20°	1163.6	21.4
20°-30°	1641.4	30.2
30°-40°	1417.0	26.1
40°-50°	634.6	11.7
50°-60°	166.1	3.1
60°-70°	10.8	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3210.7	59.0
0°-40°	4627.7	85.1
0°-60°	5428.4	99.8
0°-90°	5439.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5439.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4293	
5°	4266	406
15°	4126	1164
25°	3601	1641
35°	2314	1417
45°	793	635
55°	175	166
65°	1	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781917

CATALOG NUMBER: LER4D50D010-EC4DR7040509040-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4293.1
2.5°	4288.5
5°	4266.1
7.5°	4247.6
10°	4208.2
12.5°	4172.7
15°	4126.4
17.5°	4073.1
20°	3975.0
22.5°	3813.7
25°	3601.4
27.5°	3355.1
30°	3067.9
32.5°	2716.7
35°	2313.7
37.5°	1869.0
40°	1436.7
42.5°	1091.6
45°	792.8
47.5°	546.6
50°	373.7
52.5°	257.8
55°	175.2
57.5°	105.8
60°	54.0
62.5°	17.0
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)