

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781732

Luminaire Tested: LER4D50D010-EC4DR3540509024-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR3540509024-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3879.0 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781732

CATALOG NUMBER: LER4D50D010-EC4DR3540509024-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P781732

CATALOG NUMBER: LER4D50D010-EC4DR3540509024-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1166162
5°	1138755
10°	1026320
15°	796590
20°	451813
25°	175771
30°	65580
35°	35947
40°	23491
45°	14293
50°	9094
55°	6439
60°	4698
65°	2559
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14293 cd/sqm



TEST NUMBER: P781732

CATALOG NUMBER: LER4D50D010-EC4DR3540509024-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	954.9	24.6
10°-20°	1864.4	48.1
20°-30°	760.4	19.6
30°-40°	182.0	4.7
40°-50°	75.8	2.0
50°-60°	31.4	0.8
60°-70°	9.8	0.3
70°-80°	0.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3579.6	92.3
0°-40°	3761.6	97.0
0°-60°	3868.8	99.7
0°-90°	3879.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3879.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10673	
5°	10383	955
15°	7042	1864
25°	1458	760
35°	270	182
45°	92	76
55°	34	31
65°	10	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781732

CATALOG NUMBER: LER4D50D010-EC4DR3540509024-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	10673.2
2.5°	10609.1
5°	10382.7
7.5°	9931.0
10°	9250.6
12.5°	8292.5
15°	7042.3
17.5°	5513.2
20°	3885.8
22.5°	2477.8
25°	1458.0
27.5°	824.2
30°	519.8
32.5°	364.9
35°	269.5
37.5°	208.4
40°	164.7
42.5°	126.9
45°	92.5
47.5°	69.3
50°	53.5
52.5°	42.5
55°	33.8
57.5°	27.4
60°	21.5
62.5°	15.7
65°	9.9
67.5°	3.5
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)