

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784448

Luminaire Tested: LER4DD35BD010-EC4DR4020359027-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784448
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR4020359027-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2885.9 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784448

CATALOG NUMBER: LER4DD35BD010-EC4DR4020359027-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P784448

CATALOG NUMBER: LER4DD35BD010-EC4DR4020359027-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	734134
5°	730566
10°	690541
15°	587045
20°	400118
25°	166946
30°	52497
35°	24396
40°	13493
45°	6181
50°	3009
55°	1638
60°	852
65°	310
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6181 cd/sqm



TEST NUMBER: P784448

CATALOG NUMBER: LER4DD35BD010-EC4DR4020359027-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	622.0	21.6
10°-20°	1393.4	48.3
20°-30°	697.5	24.2
30°-40°	127.9	4.4
40°-50°	35.3	1.2
50°-60°	8.3	0.3
60°-70°	1.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2712.8	94.0
0°-40°	2840.7	98.4
0°-60°	2884.2	99.9
0°-90°	2885.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2885.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6719	
5°	6661	622
15°	5190	1393
25°	1385	697
35°	183	128
45°	40	35
55°	9	8
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784448

CATALOG NUMBER: LER4DD35BD010-EC4DR4020359027-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6719.1
2.5°	6709.3
5°	6661.0
7.5°	6507.1
10°	6224.1
12.5°	5782.9
15°	5189.8
17.5°	4418.5
20°	3441.2
22.5°	2346.1
25°	1384.8
27.5°	732.0
30°	416.1
32.5°	268.9
35°	182.9
37.5°	130.7
40°	94.6
42.5°	64.8
45°	40.0
47.5°	25.5
50°	17.7
52.5°	12.6
55°	8.6
57.5°	5.5
60°	3.9
62.5°	2.4
65°	1.2
67.5°	0.8
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)