

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784464

Luminaire Tested: LER4DD35BD010-EC4DR4020359050-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784464
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR4020359050-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3167.3 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784464

CATALOG NUMBER: LER4DD35BD010-EC4DR4020359050-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P784464

CATALOG NUMBER: LER4DD35BD010-EC4DR4020359050-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96		
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88		
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84		
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81		
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77		
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74		
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72		
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69		
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	805733
5°	801813
10°	757885
15°	644303
20°	439139
25°	183221
30°	57606
35°	26783
40°	14805
45°	6783
50°	3298
55°	1810
60°	940
65°	336
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6783 cd/sqm



TEST NUMBER: P784464

CATALOG NUMBER: LER4DD35BD010-EC4DR4020359050-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	682.6	21.6
10°-20°	1529.3	48.3
20°-30°	765.5	24.2
30°-40°	140.3	4.4
40°-50°	38.7	1.2
50°-60°	9.1	0.3
60°-70°	1.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2977.4	94.0
0°-40°	3117.7	98.4
0°-60°	3165.5	99.9
0°-90°	3167.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3167.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7374	
5°	7311	683
15°	5696	1529
25°	1520	765
35°	201	140
45°	44	39
55°	10	9
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784464

CATALOG NUMBER: LER4DD35BD010-EC4DR4020359050-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7374.4
2.5°	7363.6
5°	7310.6
7.5°	7141.7
10°	6831.1
12.5°	6346.9
15°	5696.0
17.5°	4849.5
20°	3776.8
22.5°	2574.9
25°	1519.8
27.5°	803.4
30°	456.6
32.5°	295.1
35°	200.8
37.5°	143.5
40°	103.8
42.5°	71.1
45°	43.9
47.5°	28.0
50°	19.4
52.5°	13.8
55°	9.5
57.5°	6.0
60°	4.3
62.5°	2.6
65°	1.3
67.5°	0.9
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)