

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781801

Luminaire Tested: LER4D50D010-EC4DR4540509050-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781801
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR4540509050-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5558.4 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781801

CATALOG NUMBER: LER4D50D010-EC4DR4540509050-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781801

CATALOG NUMBER: LER4D50D010-EC4DR4540509050-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		98
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77
8	85	77	72	68	84	76	71	68	75	71	68		74	70	67		73
9	82	73	68	65	81	73	68	65	72	68	65		71	67	64		71
10	79	70	65	62	78	70	65	62	69	65	62		68	64	61		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1073443
5°	1042874
10°	997751
15°	913155
20°	724450
25°	452278
30°	249286
35°	111935
40°	44087
45°	20783
50°	9859
55°	5143
60°	2535
65°	595
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20783 cd/sqm



TEST NUMBER: P781801

CATALOG NUMBER: LER4D50D010-EC4DR4540509050-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	893.4	16.1
10°-20°	2198.8	39.6
20°-30°	1741.2	31.3
30°-40°	579.8	10.4
40°-50°	115.1	2.1
50°-60°	26.1	0.5
60°-70°	3.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4833.5	87.0
0°-40°	5413.3	97.4
0°-60°	5554.5	99.9
0°-90°	5558.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5558.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9825	
5°	9508	893
15°	8073	2199
25°	3752	1741
35°	839	580
45°	134	115
55°	27	26
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781801

CATALOG NUMBER: LER4D50D010-EC4DR4540509050-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9824.6
2.5°	9760.4
5°	9508.5
7.5°	9300.7
10°	8993.1
12.5°	8583.6
15°	8072.8
17.5°	7304.7
20°	6230.6
22.5°	4950.9
25°	3751.6
27.5°	2747.1
30°	1975.9
32.5°	1343.8
35°	839.2
37.5°	497.6
40°	309.1
42.5°	203.2
45°	134.5
47.5°	86.5
50°	58.0
52.5°	38.6
55°	27.0
57.5°	17.8
60°	11.6
62.5°	6.2
65°	2.3
67.5°	0.8
70°	0.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)