

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784573

Luminaire Tested: LER4DD35BD010-EC4DR6520359030-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR6520359030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2800.2 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784573

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359030-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P784573

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	301232
5°	301472
10°	312092
15°	312605
20°	287810
25°	245223
30°	187731
35°	132622
40°	78289
45°	31784
50°	11525
55°	6420
60°	3671
65°	2017
70°	2140
75°	1646
80°	1699
85°	1504

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31784 cd/sqm



TEST NUMBER: P784573

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	265.5	9.5
10°-20°	765.8	27.3
20°-30°	918.8	32.8
30°-40°	617.5	22.1
40°-50°	184.8	6.6
50°-60°	32.6	1.2
60°-70°	9.3	0.3
70°-80°	4.5	0.2
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1950.0	69.6
0°-40°	2567.5	91.7
0°-60°	2784.9	99.5
0°-90°	2800.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2800.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2757	
5°	2749	265
15°	2764	766
25°	2034	919
35°	994	617
45°	206	185
55°	34	33
65°	8	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P784573

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2757.0
2.5°	2768.7
5°	2748.7
7.5°	2790.3
10°	2813.0
12.5°	2807.5
15°	2763.6
17.5°	2656.3
20°	2475.3
22.5°	2262.1
25°	2034.1
27.5°	1776.7
30°	1488.0
32.5°	1226.3
35°	994.3
37.5°	765.2
40°	548.9
42.5°	358.5
45°	205.7
47.5°	108.9
50°	67.8
52.5°	47.0
55°	33.7
57.5°	24.3
60°	16.8
62.5°	11.0
65°	7.8
67.5°	7.1
70°	6.7
72.5°	5.1
75°	3.9
77.5°	3.5
80°	2.7
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)