

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P781901

Luminaire Tested: LER4D50D010-EC4DR7040509024-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P781901
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D50D010-EC4DR7040509024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4406.3 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P781901

CATALOG NUMBER: LER4D50D010-EC4DR7040509024-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P781901

CATALOG NUMBER: LER4D50D010-EC4DR7040509024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56		
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	379987
5°	379037
10°	378216
15°	378110
20°	374410
25°	351710
30°	313554
35°	249999
40°	165993
45°	99247
50°	51453
55°	27050
60°	9571
65°	155
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 99247 cd/sqm



TEST NUMBER: P781901

CATALOG NUMBER: LER4D50D010-EC4DR7040509024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.7	7.5
10°-20°	942.6	21.4
20°-30°	1329.7	30.2
30°-40°	1147.9	26.1
40°-50°	514.1	11.7
50°-60°	134.6	3.1
60°-70°	8.8	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2600.9	59.0
0°-40°	3748.8	85.1
0°-60°	4397.5	99.8
0°-90°	4406.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4406.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3478	
5°	3456	329
15°	3343	943
25°	2917	1330
35°	1874	1148
45°	642	514
55°	142	135
65°	1	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P781901

CATALOG NUMBER: LER4D50D010-EC4DR7040509024-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3477.8
2.5°	3474.0
5°	3455.9
7.5°	3440.9
10°	3409.0
12.5°	3380.2
15°	3342.7
17.5°	3299.5
20°	3220.1
22.5°	3089.4
25°	2917.4
27.5°	2717.9
30°	2485.3
32.5°	2200.7
35°	1874.3
37.5°	1514.1
40°	1163.8
42.5°	884.3
45°	642.3
47.5°	442.8
50°	302.7
52.5°	208.9
55°	142.0
57.5°	85.7
60°	43.8
62.5°	13.8
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)