

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784583

Luminaire Tested: LER4DD35BD010-EC4DR6520359040-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR6520359040-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2555.6 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784583

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359040-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P784583

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359040-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		106	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	89	84	79		95	88	83	79		86	82	78		84	80	77		82	79	76
5	92	83	78	73		90	83	77	73		81	76	72		79	75	72		77	74	71
6	87	78	72	68		86	77	72	68		76	71	67		74	70	67		73	69	66
7	83	73	67	63		81	73	67	63		71	66	62		70	66	62		69	65	62
8	79	69	63	59		77	68	63	59		67	62	58		66	62	58		65	61	58
9	75	65	59	55		74	65	59	55		64	58	55		63	58	55		62	58	54
10	71	61	56	52		70	61	55	52		60	55	51		59	55	51		59	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	274911
5°	275139
10°	284832
15°	285299
20°	262660
25°	223800
30°	171330
35°	121045
40°	71443
45°	29003
50°	10522
55°	5848
60°	3365
65°	1861
70°	1949
75°	1520
80°	1573
85°	1379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29003 cd/sqm



TEST NUMBER: P784583

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359040-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.3	9.5
10°-20°	698.9	27.3
20°-30°	838.5	32.8
30°-40°	563.5	22.1
40°-50°	168.7	6.6
50°-60°	29.8	1.2
60°-70°	8.5	0.3
70°-80°	4.1	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1779.7	69.6
0°-40°	2343.2	91.7
0°-60°	2541.6	99.5
0°-90°	2555.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2555.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2516	
5°	2509	242
15°	2522	699
25°	1856	839
35°	908	564
45°	188	169
55°	31	30
65°	7	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P784583

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359040-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2516.1
2.5°	2526.9
5°	2508.6
7.5°	2546.5
10°	2567.3
12.5°	2562.3
15°	2522.2
17.5°	2424.2
20°	2259.0
22.5°	2064.5
25°	1856.4
27.5°	1621.5
30°	1358.0
32.5°	1119.2
35°	907.5
37.5°	698.3
40°	500.9
42.5°	327.2
45°	187.7
47.5°	99.4
50°	61.9
52.5°	42.9
55°	30.7
57.5°	22.2
60°	15.4
62.5°	10.0
65°	7.2
67.5°	6.4
70°	6.1
72.5°	4.6
75°	3.6
77.5°	3.2
80°	2.5
82.5°	1.8
85°	1.1
87.5°	0.7
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)