

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784587

Luminaire Tested: LER4DD35BD010-EC4DR6520359050-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P784587
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR6520359050-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2573.8 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784587

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359050-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P784587

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359050-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	276878
5°	277102
10°	286863
15°	287335
20°	264544
25°	225403
30°	172554
35°	121912
40°	71957
45°	29219
50°	10590
55°	5905
60°	3387
65°	1861
70°	1949
75°	1520
80°	1573
85°	1379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29219 cd/sqm



TEST NUMBER: P784587

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359050-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.0	9.5
10°-20°	703.9	27.3
20°-30°	844.5	32.8
30°-40°	567.5	22.1
40°-50°	169.9	6.6
50°-60°	30.0	1.2
60°-70°	8.5	0.3
70°-80°	4.2	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1792.4	69.6
0°-40°	2359.9	91.7
0°-60°	2559.8	99.5
0°-90°	2573.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2573.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2534	
5°	2526	244
15°	2540	704
25°	1870	845
35°	914	568
45°	189	170
55°	31	30
65°	7	9
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P784587

CATALOG NUMBER: LER4DD35BD010-EC4DR6520359050-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2534.1
2.5°	2544.9
5°	2526.5
7.5°	2564.7
10°	2585.6
12.5°	2580.6
15°	2540.2
17.5°	2441.5
20°	2275.2
22.5°	2079.3
25°	1869.7
27.5°	1633.1
30°	1367.7
32.5°	1127.1
35°	914.0
37.5°	703.3
40°	504.5
42.5°	329.5
45°	189.1
47.5°	100.1
50°	62.3
52.5°	43.2
55°	31.0
57.5°	22.3
60°	15.5
62.5°	10.1
65°	7.2
67.5°	6.5
70°	6.1
72.5°	4.7
75°	3.6
77.5°	3.2
80°	2.5
82.5°	1.8
85°	1.1
87.5°	0.7
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)