

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784613

Luminaire Tested: LER4DD40BD010-EC4DR2540509024-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784613
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR2540509024-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2880.3 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784613

CATALOG NUMBER: LER4DD40BD010-EC4DR2540509024-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P784613

CATALOG NUMBER: LER4DD40BD010-EC4DR2540509024-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85		
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82		
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79		
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1193597
5°	1111686
10°	792989
15°	467041
20°	290601
25°	159483
30°	72935
35°	27624
40°	12509
45°	7525
50°	3128
55°	2019
60°	1399
65°	957
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7525 cd/sqm



TEST NUMBER: P784613

CATALOG NUMBER: LER4DD40BD010-EC4DR2540509024-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	871.1	30.2
10°-20°	1179.8	41.0
20°-30°	624.4	21.7
30°-40°	154.1	5.4
40°-50°	37.6	1.3
50°-60°	9.9	0.3
60°-70°	3.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2675.3	92.9
0°-40°	2829.4	98.2
0°-60°	2876.9	99.9
0°-90°	2880.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2880.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10924	
5°	10136	871
15°	4129	1180
25°	1323	624
35°	207	154
45°	49	38
55°	11	10
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784613

CATALOG NUMBER: LER4DD40BD010-EC4DR2540509024-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	10924.3
2.5°	10744.7
5°	10135.9
7.5°	8912.6
10°	7147.5
12.5°	5403.1
15°	4128.9
17.5°	3217.9
20°	2499.3
22.5°	1874.4
25°	1322.9
27.5°	887.1
30°	578.1
32.5°	351.7
35°	207.1
37.5°	126.7
40°	87.7
42.5°	67.0
45°	48.7
47.5°	29.4
50°	18.4
52.5°	13.3
55°	10.6
57.5°	8.3
60°	6.4
62.5°	5.1
65°	3.7
67.5°	1.4
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)