

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784441

Luminaire Tested: LER4DD35BD010-EC4DR3520359050-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784441
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR3520359050-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3251.8 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784441

CATALOG NUMBER: LER4DD35BD010-EC4DR3520359050-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P784441

CATALOG NUMBER: LER4DD35BD010-EC4DR3520359050-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	977578
5°	954605
10°	860355
15°	667775
20°	378747
25°	147355
30°	54969
35°	30131
40°	19697
45°	11991
50°	7632
55°	5391
60°	3955
65°	2146
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11991 cd/sqm



TEST NUMBER: P784441

CATALOG NUMBER: LER4DD35BD010-EC4DR3520359050-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	800.5	24.6
10°-20°	1562.9	48.1
20°-30°	637.4	19.6
30°-40°	152.5	4.7
40°-50°	63.6	2.0
50°-60°	26.3	0.8
60°-70°	8.2	0.3
70°-80°	0.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3000.8	92.3
0°-40°	3153.3	97.0
0°-60°	3243.2	99.7
0°-90°	3251.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3251.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8947	
5°	8704	800
15°	5904	1563
25°	1222	637
35°	226	153
45°	78	64
55°	28	26
65°	8	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784441

CATALOG NUMBER: LER4DD35BD010-EC4DR3520359050-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	8947.2
2.5°	8893.5
5°	8703.7
7.5°	8325.1
10°	7754.7
12.5°	6951.6
15°	5903.5
17.5°	4621.7
20°	3257.4
22.5°	2077.1
25°	1222.3
27.5°	690.9
30°	435.7
32.5°	305.9
35°	225.9
37.5°	174.7
40°	138.1
42.5°	106.4
45°	77.6
47.5°	58.1
50°	44.9
52.5°	35.6
55°	28.3
57.5°	22.9
60°	18.1
62.5°	13.2
65°	8.3
67.5°	2.9
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)