

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784442

Luminaire Tested: LER4DD35BD010-EC4DR3520359050-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784442
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR3520359050-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3414.4 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784442

CATALOG NUMBER: LER4DD35BD010-EC4DR3520359050-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P784442

CATALOG NUMBER: LER4DD35BD010-EC4DR3520359050-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1026461
5°	1002337
10°	903369
15°	701166
20°	397688
25°	154721
30°	57720
35°	31638
40°	20681
45°	12593
50°	8006
55°	5658
60°	4152
65°	2249
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12593 cd/sqm



TEST NUMBER: P784442

CATALOG NUMBER: LER4DD35BD010-EC4DR3520359050-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	840.5	24.6
10°-20°	1641.0	48.1
20°-30°	669.3	19.6
30°-40°	160.2	4.7
40°-50°	66.8	2.0
50°-60°	27.6	0.8
60°-70°	8.6	0.3
70°-80°	0.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3150.8	92.3
0°-40°	3311.0	97.0
0°-60°	3405.4	99.7
0°-90°	3414.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3414.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9395	
5°	9139	841
15°	6199	1641
25°	1283	669
35°	237	160
45°	82	67
55°	30	28
65°	9	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784442

CATALOG NUMBER: LER4DD35BD010-EC4DR3520359050-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9394.6
2.5°	9338.2
5°	9138.9
7.5°	8741.4
10°	8142.4
12.5°	7299.1
15°	6198.7
17.5°	4852.8
20°	3420.3
22.5°	2181.0
25°	1283.4
27.5°	725.5
30°	457.5
32.5°	321.2
35°	237.2
37.5°	183.4
40°	145.0
42.5°	111.7
45°	81.5
47.5°	61.0
50°	47.1
52.5°	37.4
55°	29.7
57.5°	24.1
60°	19.0
62.5°	13.8
65°	8.7
67.5°	3.1
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)