

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784621

Luminaire Tested: LER4DD40BD010-EC4DR2540509030-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR2540509030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3361.3 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784621

CATALOG NUMBER: LER4DD40BD010-EC4DR2540509030-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P784621

CATALOG NUMBER: LER4DD40BD010-EC4DR2540509030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85		
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82		
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79		
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1392944
5°	1297349
10°	925436
15°	545045
20°	339133
25°	186114
30°	85122
35°	32239
40°	14605
45°	8777
50°	3638
55°	2343
60°	1639
65°	1112
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8777 cd/sqm



TEST NUMBER: P784621

CATALOG NUMBER: LER4DD40BD010-EC4DR2540509030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1016.6	30.2
10°-20°	1376.9	41.0
20°-30°	728.6	21.7
30°-40°	179.9	5.4
40°-50°	43.9	1.3
50°-60°	11.5	0.3
60°-70°	3.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3122.1	92.9
0°-40°	3302.0	98.2
0°-60°	3357.4	99.9
0°-90°	3361.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3361.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12749	
5°	11829	###
15°	4818	1377
25°	1544	729
35°	242	180
45°	57	44
55°	12	12
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784621

CATALOG NUMBER: LER4DD40BD010-EC4DR2540509030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	12748.8
2.5°	12539.2
5°	11828.7
7.5°	10401.1
10°	8341.3
12.5°	6305.5
15°	4818.5
17.5°	3755.3
20°	2916.7
22.5°	2187.4
25°	1543.8
27.5°	1035.3
30°	674.7
32.5°	410.5
35°	241.7
37.5°	147.9
40°	102.4
42.5°	78.2
45°	56.8
47.5°	34.3
50°	21.4
52.5°	15.5
55°	12.3
57.5°	9.6
60°	7.5
62.5°	5.9
65°	4.3
67.5°	1.6
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)