

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784453

Luminaire Tested: LER4DD35BD010-EC4DR4020359030-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784453
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR4020359030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3336.1 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784453

CATALOG NUMBER: LER4DD35BD010-EC4DR4020359030-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P784453

CATALOG NUMBER: LER4DD35BD010-EC4DR4020359030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	848650
5°	844521
10°	798258
15°	678622
20°	462533
25°	192986
30°	60685
35°	28197
40°	15604
45°	7154
50°	3468
55°	1905
60°	983
65°	362
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7154 cd/sqm



TEST NUMBER: P784453

CATALOG NUMBER: LER4DD35BD010-EC4DR4020359030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	719.0	21.6
10°-20°	1610.7	48.3
20°-30°	806.3	24.2
30°-40°	147.8	4.4
40°-50°	40.8	1.2
50°-60°	9.6	0.3
60°-70°	1.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3136.0	94.0
0°-40°	3283.8	98.4
0°-60°	3334.2	99.9
0°-90°	3336.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3336.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7767	
5°	7700	719
15°	5999	1611
25°	1601	806
35°	211	148
45°	46	41
55°	10	10
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784453

CATALOG NUMBER: LER4DD35BD010-EC4DR4020359030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7767.2
2.5°	7755.8
5°	7700.0
7.5°	7522.2
10°	7195.0
12.5°	6685.0
15°	5999.4
17.5°	5107.8
20°	3978.0
22.5°	2712.0
25°	1600.8
27.5°	846.2
30°	481.0
32.5°	310.8
35°	211.4
37.5°	151.1
40°	109.4
42.5°	74.9
45°	46.3
47.5°	29.5
50°	20.4
52.5°	14.5
55°	10.0
57.5°	6.4
60°	4.5
62.5°	2.7
65°	1.4
67.5°	0.9
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)