

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784478

Luminaire Tested: LER4DD35BD010-EC4DR4520359030-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784478
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR4520359030-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3436.7 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784478

CATALOG NUMBER: LER4DD35BD010-EC4DR4520359030-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P784478

CATALOG NUMBER: LER4DD35BD010-EC4DR4520359030-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		98
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77
8	85	77	72	68	84	76	71	68	75	71	68		74	70	67		73
9	82	73	68	65	81	73	68	65	72	68	65		71	67	64		71
10	79	70	65	62	78	70	65	62	69	65	62		68	64	61		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	663694
5°	644798
10°	616895
15°	564591
20°	447918
25°	279641
30°	154134
35°	69212
40°	27257
45°	12840
50°	6085
55°	3181
60°	1573
65°	362
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12840 cd/sqm



TEST NUMBER: P784478

CATALOG NUMBER: LER4DD35BD010-EC4DR4520359030-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	552.4	16.1
10°-20°	1359.5	39.6
20°-30°	1076.6	31.3
30°-40°	358.5	10.4
40°-50°	71.1	2.1
50°-60°	16.2	0.5
60°-70°	2.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2988.5	87.0
0°-40°	3347.0	97.4
0°-60°	3434.3	99.9
0°-90°	3436.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3436.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6074	
5°	5879	552
15°	4991	1359
25°	2320	1077
35°	519	359
45°	83	71
55°	17	16
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784478

CATALOG NUMBER: LER4DD35BD010-EC4DR4520359030-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6074.4
2.5°	6034.7
5°	5879.0
7.5°	5750.4
10°	5560.3
12.5°	5307.1
15°	4991.3
17.5°	4516.4
20°	3852.3
22.5°	3061.1
25°	2319.6
27.5°	1698.5
30°	1221.7
32.5°	830.8
35°	518.9
37.5°	307.7
40°	191.1
42.5°	125.7
45°	83.1
47.5°	53.5
50°	35.8
52.5°	23.9
55°	16.7
57.5°	11.0
60°	7.2
62.5°	3.8
65°	1.4
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)