

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784486

Luminaire Tested: LER4DD35BD010-EC4DR4520359040-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784486
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR4520359040-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3635.2 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784486

CATALOG NUMBER: LER4DD35BD010-EC4DR4520359040-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P784486

CATALOG NUMBER: LER4DD35BD010-EC4DR4520359040-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108	112	110	108	106		106	104	103		102	101	100		98	98	97
2	109	105	102	99	107	103	100	98		100	98	95		97	95	93		95	93	91
3	105	99	95	91	103	98	94	91		95	92	89		93	90	88		91	89	87
4	100	94	89	85	99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80	95	88	83	80		86	82	79		85	81	79		83	80	78
6	92	85	80	76	91	84	79	76		83	78	75		81	77	75		80	77	74
7	89	81	75	72	87	80	75	72		79	74	71		78	74	71		77	73	71
8	85	77	72	68	84	76	71	68		75	71	68		74	70	67		73	70	67
9	82	73	68	65	81	73	68	65		72	68	65		71	67	64		71	67	64
10	79	70	65	62	78	70	65	62		69	65	62		68	64	61		68	64	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	702033
5°	682044
10°	652531
15°	597202
20°	473789
25°	295796
30°	163028
35°	73200
40°	28825
45°	13582
50°	6442
55°	3372
60°	1661
65°	388
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13582 cd/sqm



TEST NUMBER: P784486

CATALOG NUMBER: LER4DD35BD010-EC4DR4520359040-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	584.3	16.1
10°-20°	1438.0	39.6
20°-30°	1138.8	31.3
30°-40°	379.2	10.4
40°-50°	75.2	2.1
50°-60°	17.1	0.5
60°-70°	2.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3161.1	87.0
0°-40°	3540.3	97.4
0°-60°	3632.7	99.9
0°-90°	3635.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3635.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6425	
5°	6219	584
15°	5280	1438
25°	2454	1139
35°	549	379
45°	88	75
55°	18	17
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784486

CATALOG NUMBER: LER4DD35BD010-EC4DR4520359040-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6425.3
2.5°	6383.4
5°	6218.6
7.5°	6082.7
10°	5881.5
12.5°	5613.7
15°	5279.6
17.5°	4777.3
20°	4074.8
22.5°	3237.9
25°	2453.6
27.5°	1796.6
30°	1292.2
32.5°	878.8
35°	548.8
37.5°	325.5
40°	202.1
42.5°	132.9
45°	87.9
47.5°	56.6
50°	37.9
52.5°	25.3
55°	17.7
57.5°	11.6
60°	7.6
62.5°	4.0
65°	1.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)