

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784673

Luminaire Tested: LER4DD40BD010-EC4DR3540509035-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784673
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR3540509035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3631.1 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784673

CATALOG NUMBER: LER4DD40BD010-EC4DR3540509035-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P784673

CATALOG NUMBER: LER4DD40BD010-EC4DR3540509035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1091613
5°	1065973
10°	960717
15°	745677
20°	422931
25°	164547
30°	61391
35°	33652
40°	21994
45°	13381
50°	8516
55°	6019
60°	4414
65°	2404
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13381 cd/sqm

TEST NUMBER: P784673

CATALOG NUMBER: LER4DD40BD010-EC4DR3540509035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	893.9	24.6
10°-20°	1745.2	48.1
20°-30°	711.8	19.6
30°-40°	170.3	4.7
40°-50°	71.0	2.0
50°-60°	29.4	0.8
60°-70°	9.2	0.3
70°-80°	0.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3350.8	92.3
0°-40°	3521.2	97.0
0°-60°	3621.5	99.7
0°-90°	3631.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3631.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9991	
5°	9719	894
15°	6592	1745
25°	1365	712
35°	252	170
45°	87	71
55°	32	29
65°	9	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784673

CATALOG NUMBER: LER4DD40BD010-EC4DR3540509035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9990.9
2.5°	9931.0
5°	9719.1
7.5°	9296.2
10°	8659.3
12.5°	7762.5
15°	6592.2
17.5°	5160.8
20°	3637.4
22.5°	2319.4
25°	1364.9
27.5°	771.5
30°	486.6
32.5°	341.6
35°	252.3
37.5°	195.1
40°	154.2
42.5°	118.8
45°	86.6
47.5°	64.8
50°	50.1
52.5°	39.8
55°	31.6
57.5°	25.6
60°	20.2
62.5°	14.7
65°	9.3
67.5°	3.3
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)