

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784691

Luminaire Tested: LER4DD40BD010-EC4DR4040509027-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD40BD010-EC4DR4040509027-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3616.7 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784691

CATALOG NUMBER: LER4DD40BD010-EC4DR4040509027-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P784691

CATALOG NUMBER: LER4DD40BD010-EC4DR4040509027-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96			
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92			
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88			
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84			
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81			
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77			
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74			
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72			
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69			
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	920030
5°	915560
10°	865403
15°	735700
20°	501438
25°	209225
30°	65782
35°	30571
40°	16916
45°	7757
50°	3757
55°	2057
60°	1071
65°	388
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7757 cd/sqm



TEST NUMBER: P784691

CATALOG NUMBER: LER4DD40BD010-EC4DR4040509027-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	779.5	21.6
10°-20°	1746.2	48.3
20°-30°	874.1	24.2
30°-40°	160.2	4.4
40°-50°	44.2	1.2
50°-60°	10.4	0.3
60°-70°	2.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3399.8	94.0
0°-40°	3560.0	98.4
0°-60°	3614.6	99.9
0°-90°	3616.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3616.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8420	
5°	8348	779
15°	6504	1746
25°	1736	874
35°	229	160
45°	50	44
55°	11	10
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784691

CATALOG NUMBER: LER4DD40BD010-EC4DR4040509027-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8420.5
2.5°	8408.2
5°	8347.7
7.5°	8154.9
10°	7800.2
12.5°	7247.3
15°	6504.0
17.5°	5537.4
20°	4312.6
22.5°	2940.1
25°	1735.5
27.5°	917.4
30°	521.4
32.5°	337.0
35°	229.2
37.5°	163.8
40°	118.6
42.5°	81.2
45°	50.2
47.5°	32.0
50°	22.1
52.5°	15.7
55°	10.8
57.5°	6.9
60°	4.9
62.5°	3.0
65°	1.5
67.5°	1.0
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)