

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P784520

Luminaire Tested: LER4DD35BD010-EC4DR5520359027-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P784520
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4DD35BD010-EC4DR5520359027-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2501.0 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P784520

CATALOG NUMBER: LER4DD35BD010-EC4DR5520359027-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P784520

CATALOG NUMBER: LER4DD35BD010-EC4DR5520359027-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94						
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87						
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81						
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75						
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70						
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65						
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61						
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57						
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54						
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	306422
5°	294244
10°	293142
15°	284722
20°	255289
25°	210985
30°	159370
35°	115563
40°	73954
45°	33778
50°	11049
55°	4762
60°	2054
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33778 cd/sqm



TEST NUMBER: P784520

CATALOG NUMBER: LER4DD35BD010-EC4DR5520359027-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.3	10.2
10°-20°	696.7	27.9
20°-30°	794.0	31.7
30°-40°	540.5	21.6
40°-50°	186.3	7.4
50°-60°	25.8	1.0
60°-70°	2.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1746.0	69.8
0°-40°	2286.5	91.4
0°-60°	2498.5	99.9
0°-90°	2501.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2501.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2804	
5°	2683	255
15°	2517	697
25°	1750	794
35°	866	541
45°	219	186
55°	25	26
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P784520

CATALOG NUMBER: LER4DD35BD010-EC4DR5520359027-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2804.5
2.5°	2740.2
5°	2682.8
7.5°	2654.7
10°	2642.2
12.5°	2600.5
15°	2517.1
17.5°	2384.7
20°	2195.6
22.5°	1977.4
25°	1750.1
27.5°	1513.4
30°	1263.2
32.5°	1051.2
35°	866.4
37.5°	690.5
40°	518.5
42.5°	359.3
45°	218.6
47.5°	117.8
50°	65.0
52.5°	38.6
55°	25.0
57.5°	16.0
60°	9.4
62.5°	4.2
65°	1.0
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)